

# Small size, big power

# Fast, accurate, versatile XRF analysis

When versatility, low limits of detection (LODs) and high sample throughput are critical, industrial businesses rely on the Thermo Scientific™ Niton™ XL5 Plus handheld XRF analyzer. Providing customers with solutions designed to meet their most demanding applications, the Niton XL5 Plus analyzer maximizes performance and productivity.

## **Applications**

- · Verification of metals and alloys in manufacturing operations
- Non-destructive field inspections for positive material identification
- · Point-and-shoot sorting at scrap recycling operations
- Measurement of single or multi-layer coat weight and coating thickness in surface treatment control
- Precious metal assay of bullion and jewelry
- Real-time geochemical analysis for mining exploration
- · On-site heavy metal screening of polluted soils
- Screening for hazardous substances in consumer goods
- Custom applications on demand

#### Analytical performance

Designed to return lab-quality results, the Niton XL5 Plus analyzer's low limits of detection allow operators to scan a broad range of materials for diverse applications. Identify pure metals and alloys, obtain geochemical data, screen for heavy metals or determine plating and coating thickness. From metals to mining, and everything in between, this analyzer is ready to work.

#### Rapid results

Powered by a 5W X-ray tube, the Niton XL5 Plus analyzer generates fast and accurate results. An upgraded graphene window ensures optimum sensitivity for each measurement - even light elements. Results are displayed in real time, enabling you to make faster decisions. And with a standard system health check designed to verify operating parameters, your device will operate smoothly.

### Size and weight

Make light work of heavy industrial tasks utilizing the Niton XL5 Plus analyzer. Weighing an industry leading 2.8 pounds (1.3 kilograms), this analyzer is the lightest handheld XRF analyzer available for elemental determination and alloy identification. Its small footprint and featherweight design reduce operator fatigue while increasing productivity.







The Niton XL5 Plus analyzer in use, analyzing a tight weld in an oil refinery.

#### Design

Tight spots are no match for the Niton XL5 Plus analyzer. Discover expanded field use with improved compact geometry and ergonomics. Tight welds, corners, and joints are no longer defined as awkward test spots with the Niton XL5 Plus analyzer. Standard ProGuard detector protection also reduces risk when measuring sharp items.

#### **Functionality**

Vivid new icons and an application interface ease navigation and configuration. Swipe and touchscreen functionalites work even with a gloved hand. Optional directional keys provide added usability. A hot swap battery keeps you up and running when it's time to replace a low battery. Micro and macro cameras enable precise sample positioning and collect images for better record keeping. Finally, WiFi accessibility automatically transmits data from your device to PC.

1. The Thermo Scientific™ Niton™ XL5 Plus handheld XRF analyzer weighs 2.8lbs (1.3 kg). The Niton XL5 Plus is the smallest and lightest handheld XRF analyzer leveraging X-ray tube technology.

thermo scientific

Weight	2.8 lbs with battery (1.3 kg)	
Dimensions	9.54 x 8.19 x 2.67 in (242.56 x 208.17 x 67.90 mm)	
X-Ray Source	X-Ray Tube: Ag anode (6-50kV, 0-500uA, 5W max)	
t riay course	Filter: Six (6) position filter wheel for enhanced spectral range coverage	
	Current: Dynamically adjustable current for optimal sensitivity on every analysis	
Detector	High count rate, high resolution, extra large area silicon drift detector (1µm graphene window)	
	Detector ProGuard protection included	
Spot Size	Standard: 8mm collimation	
A 1 11 1 1 D	Optional: 3mm small-spot collimation  Mg LL (ultra law light element detection). No (expectrum based detection).	
Analytical Range	Mg-U (ultra low light element detection), Na (spectrum based detection)	
Calibration Modes	General Metals, Precious Metals, Light Metal Quick Sort, Coatings, Mining, Soils, Electronic Alloys, Plastics, Industrial Lead in Paint, Spectral Fingerprint, TestAll™	
Libraries	Default alloy libraries based on SAE, AISI, ASTM, AA,DIN, GB standards	
0 1 0: 1	Users may create, clone and edit libraries	
System Check	Built-in standardization and health check verifies system integrity and operating conditions	
IP Rating	IP54 (splash and dust proof)	
Operating Environment	Temperature: 0°C to 50°C (external fan recommended when ambient temperature is greater than 33°C)	
	Humidity: 10% to 90% relative humidity non-condensing	
Display	Tilting, color, resistive touchscreen display	
Power	12V lithium-ion battery, or 12V DC, 3A, 3.6W power supply	
	Hot swap functionality keeps analyzer powered during battery replacements	
Macro Camera	Integrated CCD macro camera for capturing overview images of parts and tagging	
	measurement locations	
Micro Camera	Integrated CCD micro camera for locating and recording measurement positions	
Global Positioning	Internal GPS and optional external GPS (via Bluetooth)	
System	GPS data included with sample information	
Bluetooth	Supports print functionality, external GPS connectivity and barcode reader	
Memory / Data Storage	512 MB internal system memory / 16 GB industrial grade storage Stores approximately 130,000 readings with spectra (fewer if macro and micro images are saved)	
Data Entry	Touchscreen keyboard	
Data Tunasfan	User customizable data entry	
	Optional wireless remote barcode reader	
Data Transfer	WiFi, USB-c	
Operating System	Linux	
Support Software	NitonConnect PC software	
Security	Password-protected user security	
Languages	English, Chinese, Spanish, Portuguese, Russian, Japa	
Standard Accessories	Locking shielded carrying case	Check samples
	Two (2) lithium-ion battery packs One (1) 110/220 VAC battery charger/ AC adaptor	Safety lanyard PC connection cable (USB)
Optional Accessories	Thermo Scientific™ portable test stand	Thermo Scientific™ soil guard
Optional Accessories	Thermo Scientific™ mini test stand	Thermo Scientific™ helt holster
	Thermo Scientific™ backscatter shield	Bluetooth printer :
	Thermo Scientific™ hotwork stand off	Bluetooth printer Solve
Compliance	Compliance CE, RoHS, FCC, Industry Canada, Safety to IEC 61010 1:2010	
	Varies by region. Contact your local distributor.	

جهت کسب اطلاعات بیشتر با ما تماس بگیرید: ۹۱۲۱۰۲۵۲۲۹ - ۸۸۶۳۴۹۵۴

Learn more at thermofisher.com/nitonxl5plus

